

RM-95 Lighted RimFree™



The **Lighted RimFree™** is a stylish 2x hand-held magnifier with two super-bright LED lights to ensure bright, clear viewing even in low light. The high quality acrylic lens provides a crisp, clear image while remaining lightweight and easy to hold. The twin LED lights are bright and cool, and illuminate the reading surface evenly with no glare. The ergonomically designed handle fits perfectly in your hand for trouble-free, comfortable viewing.

Instructions:

- 1) Remove tab from battery compartment (located underneath handle) to activate battery connection. This tab can be pulled out without removing the battery door.
- 2) Slide switch located on side of handle forward to activate LED lights.
- 3) Hold magnifier at a comfortable viewing distance over the surface to be viewed.
- 4) To conserve battery strength make sure to turn off LED lights when not in use.

To Replace Batteries:

Loosen screw and remove battery door from bottom of handle. Pull red tab to dislodge used batteries. Carefully follow diagram printed on bottom of battery compartment to insert new batteries in correct direction. Replace battery cover when finished. This item uses 3 1.5V silver oxide button-cell/watch batteries (model 389 / SP389 / D389).

Batteries are included.